

Service Bulletin

#FRSB0022

Date of Bulletin: October 9, 2008
Effective Date: October 9, 2008
Pump Series Affected: Series 300V & 700V
Affected Components: Anti-siphon Valve Assembly
Subject: Anti-siphon Valves
Issuing Authority: Marketing

Anti-Siphon Valves on the 300V and 700V Series Pumps

Beginning October 9, 2008, Tuthill Transfer Systems will not be installing the anti-siphon valve assembly in the discharge side of the pump. Do not remove the ¼" plug from the discharge, unless you have installed Return Line Kit 700KTH1067.

Manuals will include an identification sticker that reads, "Vacuum Breaker Not Included".

Tuthill Transfer Systems will continue to evaluate the function of the anti-siphon valve, and improve it as necessary to accomplish the things our customers' request. As these improvements become available, a notice will be sent to all of our valued distribution partners.

Please contact your Sales Representative or our Customer Service Department if you have any questions at 800-634-2695.

Sincerely,

Jay Boester
Product Manager
Tuthill Transfer Systems